

SNRO	Tuote	CPR-luokka	Pakkaus	Vakio- pituus (m)
0602125	MCMK 2x6/6 RE PEX K8/500 Eca	Eca	K8	500
0602126	MCMK 2x10/10 RM PEX K9/500 Eca	Eca	K9	500
0601915	MCMK 2x16/16 RM PEX K14/1000 Eca	Eca	K14	1000
0602152	MCMK 3x1,5/1,5 K8/1000 Eca	Eca	K8	1000
0602153	MCMK 3x2,5/2,5 K8/1000 Eca	Eca	K8	1000
0602155	MCMK 3x6/6 RE PEX K8/500 Eca	Eca	K8	500
0602156	MCMK 3x10/10 RM PEX K9/500 Eca	Eca	K9	500
0602157	MCMK 3x16/16 RM PEX K11/500 Eca	Eca	K11	500
0602172	MCMK 4x1,5/1,5 K8/1000 Eca	Eca	K8	1000
0602131	MCMK 4x1,5/1,5 PK150 Eca	Eca	Pienkela	150
0602192	MCMK 4x1,5/1,5 R100 Eca	Eca	Rengas	100
0601957	MCMK 4x1,5/1,5 R50 Eca	Eca	Rengas	50
0602143	MCMK 4x2,5/2,5 K9/1000 Eca	Eca	K9	1000
0602144	MCMK 4x2,5/2,5 PK150 Eca	Eca	Pienkela	150
0602193	MCMK 4x2,5/2,5 R100 Eca	Eca	Rengas	100
0601959	MCMK 4x2,5/2,5 R50 Eca	Eca	Rengas	50
0602142	MCMK 4x6/6 PEX K6M/200	Eca	K6M	200
0602145	MCMK 4x6/6 PEX K8/500 Eca	Eca	K8	500
0602146	MCMK 4x10/10 RM PEX K11/500 Eca	Eca	K11	500
0602147	MCMK 4x16/16 RM PEX K11/500 Eca	Eca	K11	500
0602030	MCMK-HF C-PRo 2x1,5/1,5 K7/1000	Cca-s1,d1,a1	K7	1000
0602031	MCMK-HF C-PRo 2x1,5/1,5 R100	Cca-s1,d1,a1	Rengas	100
0602032	MCMK-HF C-PRo 2x2,5/2,5 K8/1000	Cca-s1,d1,a1	K8	1000
0602033	MCMK-HF C-PRo 2x2,5/2,5 R100	Cca-s1,d1,a1	Rengas	100
0602034	MCMK-HF C-PRo 2x6/6 K8/500	Cca-s1,d1,a1	K8	500
0602035	MCMK-HF C-PRo 2x10/10 RM K9/500	Cca-s1,d1,a1	K9	500
0602036	MCMK-HF C-PRo 2x16/16 RM K14/1000	Cca-s1,d1,a1	K14	1000
0602010	MCMK-HF C-PRo 4x1,5/1,5 K1000	Cca-s1,d1,a1	K8	1000
0602027	MCMK-HF C-PRo 4x1,5/1,5 R100	Cca-s1,d1,a1	Rengas	100
0602014	MCMK-HF C-PRo 4x2,5/2,5 K1000	Cca-s1,d1,a1	K9	1000
0602028	MCMK-HF C-PRo 4x2,5/2,5 R50	Cca-s1,d1,a1	Rengas	50
0624070	MCMK-HF C-PRo 4x6/6 R50	Cca-s1,d1,a1	Rengas	50
0602015	MCMK-HF C-PRo 4x6/6 K9/500	Cca-s1,d1,a1	K9	500
0602011	MCMK-HF C-PRo 4x10/10 RM K500	Cca-s1,d1,a1	K11	500
0602013	MCMK-HF C-PRo 4x16/16 RM K500	Cca-s1,d1,a1	K11	500
0624089	MCMK-HF Dca 3x2,5/2,5 K7/500	Dca-s2,d2,a1	K7	500
0624090	MCMK-HF Dca 3x6/6 K8/500	Dca-s2,d2,a1	K8	500
0624091	MCMK-HF Dca 3x10/10 RM K9/500	Dca-s2,d2,a1	K9	500
0624092	MCMK-HF Dca 3x16/16 RM K10/500	Dca-s2,d2,a1	K10	500