

K-kelojen mitat ja painot

Tyyppi	Mitat					Paino	Kantavuus
Puiset toimituskelat	A	B	C	D	E	kg/kpl	kg
K6	600	468	250	400	75	12	300
K7	700	580	325	500	75	20	400
K8	800	580	375	500	75	25	500
K9	900	630	425	550	75	34	600
K11	1100	762	575	650	106	55	850
K12	1200	982	675	850	106	90	1500
K14	1400	982	800	850	106	115	2000
K16	1600	1018	950	850	106	195	2500
K18	1800	1075	1100	850	132	230	3000
K20	2000	1190	1300	1000	132	340	3500
K22	2200	1190	1400	1000	132	410	4500
K24	2400	1205	1400	1000	132	450	5000
K26	2600	1448	1500	1200	132	900	10000
K28	2800	1610	1500	1350	132	1180	12000
K30	3000	1800	1500	1500	132	1500	13000

