

SNRO	Tuote	CPR-luokka	Pakkaus	Vakio-pituus (m)
0406722	MMJ 3x1,5 S R100 Eca	Eca	Rengas	100
0406752	MMJ 3x1,5 S R50 Eca	Eca	Rengas	50
0456777	MMJ 3x1,5 S K6/500 Eca	Eca	K6	500
0456772	MMJ 3x1,5 S PK300 Eca	Eca	Pienkela	300
0406723	MMJ 3x2,5 S R100 Eca	Eca	Rengas	100
0406753	MMJ 3x2,5 S R50 Eca	Eca	Rengas	50
0456778	MMJ 3x2,5 S K6/500 Eca	Eca	K6	500
0456773	MMJ 3x2,5 S PK200 Eca	Eca	Pienkela	200
0406742	MMJ 5x1,5 S R100 Eca	Eca	Rengas	100
0406762	MMJ 5x1,5 S R50 Eca	Eca	Rengas	50
0456794	MMJ 5x1,5 S K6/500 Eca	Eca	K6	500
0456792	MMJ 5x1,5 S PK200 Eca	Eca	Pienkela	200
0406743	MMJ 5x2,5 S R50 Eca	Eca	Rengas	50
0456795	MMJ 5x2,5 S K7/500 Eca	Eca	K7	500
0456793	MMJ 5x2,5 S PK150 Eca	Eca	Pienkela	150
0403355	XMJ-HF Dca 2x1,5 N 500V K6/500	Dca-s2,d2,a1	K6	500
0403356	XMJ-HF Dca 3x1,5 S 500V R100	Dca-s2,d2,a1	Rengas	100
0403357	XMJ-HF Dca 3x1,5 S 500V K6/500	Dca-s2,d2,a1	K6	500
0406304	XMJ-HF Dca 3x1,5 S 500V K6M/500	Dca-s2,d2,a1	K6M	500
0403358	XMJ-HF Dca 3x1,5 S 500V PK300	Dca-s2,d2,a1	Pienkela	300
0403359	XMJ-HF Dca 3x2,5 S 500V R100	Dca-s2,d2,a1	Rengas	100
0403360	XMJ-HF Dca 3x2,5 S 500V K6/500	Dca-s2,d2,a1	K6	500
0406305	XMJ-HF Dca 3x2,5 S 500V K6M/500	Dca-s2,d2,a1	K6M	500
0403361	XMJ-HF Dca 3x2,5 S 500V PK200	Dca-s2,d2,a1	Pienkela	200
0403363	XMJ-HF Dca 5x1,5 S 500V R100	Dca-s2,d2,a1	Rengas	100
0403364	XMJ-HF Dca 5x1,5 S 500V K6/500	Dca-s2,d2,a1	K6	500
0406306	XMJ-HF Dca 5x1,5 S 500V K6M/500	Dca-s2,d2,a1	K6M	500
0403365	XMJ-HF Dca 5x1,5 S 500V PK200	Dca-s2,d2,a1	Pienkela	200
0403366	XMJ-HF Dca 5x2,5 S 500V R50	Dca-s2,d2,a1	Rengas	50
0403367	XMJ-HF Dca 5x2,5 S 500V K6/500	Dca-s2,d2,a1	K6	500
0406307	XMJ-HF Dca 5x2,5 S 500V K6M/500	Dca-s2,d2,a1	K6M	500
0403368	XMJ-HF Dca 5x2,5 S 500V PK150	Dca-s2,d2,a1	Pienkela	150

SNRO	Tuote	CPR-luokka	Pakkaus	Vakio-pituus (m)
0401606	XMJ-HF Dca 7x1,5 S 500V colour PK150	Dca-s2,d2,a1	Pienkela	150
0401627	XMJ-HF Dca 7x1,5 S 500V colour R50	Dca-s2,d2,a1	Rengas	50
0413089	XMJ-HF Dca 3x1,5 S MUSTA 500V PK300	Dca-s2,d2,a1	Pienkela	300
0413090	XMJ-HF Dca 3x2,5 S MUSTA 500V PK200	Dca-s2,d2,a1	Pienkela	200
0413091	XMJ-HF Dca 5x1,5 S MUSTA 500V PK200	Dca-s2,d2,a1	Pienkela	200
0413092	XMJ-HF Dca 5x2,5 S MUSTA 500V PK150	Dca-s2,d2,a1	Pienkela	150
0413063	AFUX-HF C-PRo 2x1,5 N 500V PK300	Cca-s1,d1,a1	Pienkela	300
0413095	AFUX-HF C-PRo 2x2,5 N 500V PK200	Cca-s1,d1,a1	Pienkela	200
0403369	AFUX-HF C-PRo 3x1,5 S 500V K6M/500	Cca-s1,d1,a1	K6M	500
0403370	AFUX-HF C-PRo 3x1,5 S 500V PK300	Cca-s1,d1,a1	Pienkela	300
0403371	AFUX-HF C-PRo 3x1,5 S 500V R100	Cca-s1,d1,a1	Rengas	100
0401617	AFUX-HF C-PRo 3x1,5 N 500V PK300	Cca-s1,d1,a1	Pienkela	300
0403374	AFUX-HF C-PRo 3x2,5 S 500V K6M/500	Cca-s1,d1,a1	K6M	500
0403375	AFUX-HF C-PRo 3x2,5 S 500V PK200	Cca-s1,d1,a1	Pienkela	200
0403379	AFUX-HF C-PRo 3x2,5 S 500V R100	Cca-s1,d1,a1	Rengas	100
0403380	AFUX-HF C-PRo 3x6 S 500V K6M/400	Cca-s1,d1,a1	K6M	400
0403362	AFUX-HF C-PRo 4x1,5 S 500V PK250	Cca-s1,d1,a1	Pienkela	250
0413096	AFUX-HF C-PRo 4x2,5 S 500V PK150	Cca-s1,d1,a1	Pienkela	150
0403381	AFUX-HF C-PRo 5x1,5 S 500V K6M/500	Cca-s1,d1,a1	K6M	500
0403382	AFUX-HF C-PRo 5x1,5 S 500V PK200	Cca-s1,d1,a1	Pienkela	200
0403383	AFUX-HF C-PRo 5x1,5 S 500V R100	Cca-s1,d1,a1	Rengas	100
0401618	AFUX-HF C-PRo 5x1,5 N 500V PK200	Cca-s1,d1,a1	Pienkela	200
0403384	AFUX-HF C-PRo 5x2,5 S 500V K6M/500	Cca-s1,d1,a1	K6M	500
0403385	AFUX-HF C-PRo 5x2,5 S 500V PK150	Cca-s1,d1,a1	Pienkela	150
0403386	AFUX-HF C-PRo 5x2,5 S 500V R50	Cca-s1,d1,a1	Rengas	50
0403387	AFUX-HF C-PRo 5x6 S 500V K6M/250	Cca-s1,d1,a1	K6M	250
0403388	AFUX-HF C-PRo 3x6 S 1kV K500	Cca-s1,d1,a1	K8	500
0403389	AFUX-HF C-PRo 3x10 S 1kV K400	Cca-s1,d1,a1	K8	400
0403390	AFUX-HF C-PRo 5x6 S 1kV K500	Cca-s1,d1,a1	K8	500
0403391	AFUX-HF C-PRo 5x6 S 1kV K6M/200	Cca-s1,d1,a1	K6M	200
0403392	AFUX-HF C-PRo 5x10 S 1kV K250	Cca-s1,d1,a1	K8	250
0403393	AFUX-HF C-PRo 5x16 S 1kV K250	Cca-s1,d1,a1	K9	250
0403394	AFUX-HF C-PRo 5x25 S 1kV K250	Cca-s1,d1,a1	K11	250

SNRO	Tuote	CPR-luokka	Pak-kaus	Vakiopi-tuus (m)
0406725	MMJ 3x6 S R50 Eca	Eca	Rengas	50
0456725	MMJ 3x6 S K8/500 Eca	Eca	K8	500
0406732	MMJ 4x1,5 S R100 Eca	Eca	Rengas	100
0456782	MMJ 4x1,5 S PK250 Eca	Eca	Pienkela	250
0406745	MMJ 5x6 S R50 Eca	Eca	Rengas	50
0456746	MMJ 5x6 S K6M/200 Eca	Eca	K6M	200
0456745	MMJ 5x6 S K8/500 Eca	Eca	K8	500
0406746	MMJ 5x10 S K8/250 Eca	Eca	K8	250
0406747	MMJ 5x16 S K9/250 Eca	Eca	K9	250
0406422	MMJ 3x1,5 N R100 Eca	Eca	Rengas	100
0406442	MMJ 5x1,5 N R100 Eca	Eca	Rengas	100
0413044	MJAM-HF Dca 3x1,5 S K6/500 EQLQ	Dca-s2,d2,a2	K6	500
0413045	MJAM-HF Dca 3x2,5 S K6/500 EQLQ	Dca-s2,d2,a2	K6	500
0413046	MJAM-HF Dca 5x1,5 S K6/500 EQLQ	Dca-s2,d2,a2	K6	500
0413047	MJAM-HF Dca 5x2,5 S K7/500 EQLQ	Dca-s2,d2,a2	K7	500
0413048	MJAM-HF Dca 7x1,5RM S K7/500 FQLQ	Dca-s2,d2,a2	K7	500
0413049	MJAM-HF Dca 7x2,5RM S K8/500 FQLQ	Dca-s2,d2,a2	K8	500
0413093	MJAM-HF Com Dca 3G2,5+2x1 K7/500 EQLQ	Dca-s2,d2,a1	K7	500
0413094	MJAM-HF Com Dca 5G2,5+2x1 K8/500 EQLQ	Dca-s2,d2,a1	K8	500